



EDUCTOR v QUEX ED COMPARISON

QX World's newest product line is out – **practices all around the globe are embracing the new generation of QX's premium holistic healing devices.**

Why miss out?

QUEX ED is your ultimate choice to up your therapeutic game – it is like the EDUCTOR supercharged, ingeniously designed to expand your expertise.

Trade in your old EDUCTOR device and **get an exclusive discount on QUEX ED.**



EDUCTOR

0 Hz - 2.000 kHz

COMPARED PARAMETER

Frequency range

QUEX ED

0 Hz - 2.500 kHz

A higher range of frequencies mean that a wider spectrum of stress-related issues can be tackled through focused training. Being able to reach higher frequencies enables the user to increase efficiency in rational, emotional and spiritual trainings.

Year 2012

Hardware components

Year 2021

QUEX ED is made of the highest quality components available on the market. QX World is committed to building cutting-edge devices and to keeping up with the latest manufacturing trends and standards, so that all the latest devices can deliver precise information and generate even more specific frequencies! For example, if you can work with two signal generators with four decimal places precision, the trained frequency is purer than the frequency that can work with two decimal places.

Old processor

Communication speed device/computer

New Processor

The more you can do in a given timeframe, the more you can help your clientele. Due to our state-of-the-art optimization measures, QUEX ED easily outperforms our older product lines and even QUEX S in means of calculation and cross-device communication.

1

Sampling function increasement

12

Sampling streamlines the way QUEX ED processes signals. Samples of skin resistance, brain waves, ECG, EMG, etc. are taken at different times during the measurement and training, enabling constant cross-referencing and averaging the different measurements with radically increased precision, a trait unique in our industry!

EDUCTOR

Last-gen Plate

COMPARED PARAMETER

Testing Plate

QUEX ED

Next-gen Plate

QUEX ED's test plate has been redesigned for seamless connection of accessories, that are connected through safety banana plugs, for increased safety. Furthermore, it can interpret the signals sent and received in a higher resolution than EDUCTOR.

8 bytes AD Converter

Signal processing speed

20 bytes AD Converter

The faster data is collected and analysed, the faster the training can induce positive effects in the client. Thanks to the increased bandwidth of our AD converters, signal processing speed is up by more than 100%!